## **Pressure Control Valves**

### Pressure Reducing Valves DM 152

Valve for Hygiene Applications | Ultrapure Media



#### **Technical Data**

Connection DN 15 - 50 Nominal Pressure PN 2.5 - 10 Inlet Pressure up to 8 bar **Outlet Pressure** 0.3 - 5K<sub>vs</sub>-Value  $2 - 7 \text{ m}^3/\text{h}$ Temperature 180 °C

Medium liquids, gases and steam

### Description

Self-acting pressure reducers are simple control valves offering accurate control while being easy to install and maintain. They control the pressure downstream of the valve without requiring pneumatic or electrical control elements.

The DM 152 pressure reducing valve is a diaphragm-controlled spring-loaded proportional control valve which is primarily used for hygienic applications in the food processing and pharmaceutical industries. A PTFE protective foil renders the diaphragm physiologically safe and steamproof up to 180 °C. The valve does not require an external pilot line.

This valve is manufactured from deep-drawn stainless steel featuring excellent corrosion resistance. It contains virtually no dead pockets and is suitable for use in CIP and SIP systems. The angled design allows complete draining.

The spring module comprising spring cap, spring, adjusting screw, diaphragm and internal components, is connected to the valve body only by means of a clamp ring and two bolts. Changing the diaphragm or the complete spring assembly for a different control pressure range is extremely simple and does not call for special tools. The same applies to servicing and maintenance.

Changing the control pressure setting does not affect the height of the valve (non rising adjusting screw).

The outlet pressure to be controlled is balanced across the control unit by the force of the valve spring (set pressure). As the outlet pressure rises above the pressure set using the adjusting screw, the valve cone moves towards the seat and the volume of medium is reduced. As the outlet pressure drops, the valve control orifice increases; when the pipeline is depressurised, the valve is open. Rotating the adjusting screw clockwise increases the outlet pressure.

These valves are no shut-off elements ensuring a tight closing of the valve. In accordance with DIN EN 60534-4 and/or ANSI FCI 70-2 they may feature a leakage rate in closed position in compliance with the leakage classes III optional V:

Leakage class III (metal sealing cone) =  $0.1 \% K_{vs}$  value

Leakage class V (soft seal cone) =  $1.8 \times 10^{-5} \times \Delta p \times D^*$  [l/h] \*D=seat diameter

## Standard

- all stainless steel construction
- clamping flanges DIN 32676
- non rising adjusting screw quick-release body clamp ring

#### **Options**

- polished version for food, pharmaceutical and superclean applications surface roughness Ra  $\leq 0.25$  oder 0.4 oder 0.8  $\mu m$
- diaphragm protected by PTFE foil
- soft seal
- pneumatic actuation for toxic or hazardous media: sealed spring cap complete with leakage line connection (incl. sealed adjusting screw). Must be installed with a leakage line capable of draining leaking medium safely and without
- various diaphragm and seal materials suitable for your medium
- special connections: Aseptic, ANSI or DIN flanges, NPT, welding spigots; other connections on request
- special versions on request

Operating instructions, know how and safety instructions must be observed. All the pressure has always been indicated as overpressure. We reserve the right to alter technical specifications without notice.



K <sub>vs</sub> -Values [m³/h]						
nom. diam. DN	15	20	25	32	40	50
K <sub>vs</sub> -value m <sup>3</sup> /h	2	3	4	5	6	7

Setting Ranges [bar] and Nominal Pressure PN							
outlet press. bar	1 - 5	0.8 - 2.5	0.3 - 1.1				
PN	10 / 10	10 / 6	10 / 2.5				

# **Pressure Control Valves**

## **Pressure Reducing Valves DM 152**

Valve for Hygiene Applications | Ultrapure Media



Materials	
Body, Spring Cap, Internals	CrNiMo-steel
Spring	CrNi-steel
Valve Seal	optional soft seal
Diaphragm	FPM
Protection Foil (for diaphragm)	PTFE

Dimensions [mm]								
pressure range	size	nominal diameter DN						
[bar]		15	20	25	32	40	50	
0.8 - 2.5 1 - 5	AE <sub>1</sub>	90	90	90	120	120	120	
	AE <sub>2</sub>	90/100/110 *		90	120	120	120	
	C	200	200	200	200	200	200	
	D	138	138	138	138	138	138	

\* dimensions can vary according to type of connection, please inquire

Dimensions [mm]								
pressure range	size	nominal diameter DN						
[bar]		15	20	25	32	40	50	
0.3 - 1.1	AE <sub>1</sub>	120	120	120	120	120	120	
	AE <sub>2</sub>	120/140 *		120	120	120	120	
	C	200	200	200	200	200	200	
	D	200	200	200	200	200	200	

\* dimensions can vary according to type of connection, please inquire


Weights [kg]								
pressure range	nominal diameter DN							
[bar]	15	20	25	32	40	50		
0.8 - 2.5	2	2	2	2.5	2.5	3		
1 - 5	2	2	2	2.5	2.5	3		
0.3 - 1.1	3	3	3	3.5	3.5	4		

## **Customs Tariff Number**


84811019

Special designs on request.

The pressure has always been indicated as overpressure. Mankenberg reserves the right to alter or improve the designs or specifications of the products described herein without notice.



## **Recommended Installation**



- 1 Strainer
- 2 Shutoff valves
- 3 Pressure Reducer
- 4 Safety Valve use MANKENBERG-Products
- 5 Pressure Gauge
  - Leakage Line G 1/8 (option)

 $AE_1$ 

 $AE_2$ 

